



The **Polimask 2000 Beta** is a one size half mask, available in EDPM and silicone rubber, complying with EN 140. **The Polimask Beta** is equipped with two filters of the **200 series**.

MAIN FEATURES

- The shape of the facepiece has been designed with the aid of computerised systems which have utilised the anthropometrical data of the face shape of thousands of soldiers taken from the army thus providing a wide variety of face dimensions.
- The result is a half mask which perfectly fits to a all face shapes.

 The seal round the pass has been improved thanks to a foldi
- The seal round the nose has been improved thanks to a folding groove which adapts all nose shapes.
- Polimask 2000 can be used by operators who wear glasses as they
 do not interfere with the seal of the half mask and in the meantime
 the exhaled air expelled to the external atmosphere do not cause
 the misting of the lense.
- The front frame allows a floating sealing. The elastic harness is inserted into a stiff part fastened to the exhalation valve group which covers the mouth. The elastic strength of the harness is uniformly distributed on the face seal which is able to float and guarantee a perfect sealing. The harness is made of an elastic fabric which does not capture the hair, does not cause a bothersome sensation of

- warmth on the skin of the neck.
- The four adjustments of the front frame are self-regulating. The harness can be adjusted by the operator pulling or loosing the straps through the end buckles located on the neck. This way the operator will never have the final part of the harness in front of the facepiece thus allowing a free vision field.
- Hygienical form guard kits are available on request. They have to be positioned on the facepiece seal after any use and cleaning of the mask. In so doing the parts in contact with the face are always hygienically protected.
- The harness is equipped with two slots in which it is possible to insert a plastic flat arrow bearing the name of the operator, the date of the first day of use of the mask, the name of department or other useful information.
- A kit of ten plastic plates and a permanent marker are available on request.

CODES

Polimask BETA EPDM	Cod. 43362109
Polimask BETA SILICONE	Cod. 43362111

